

Micrometer

With V-anvil

Mitutoyo

Application:

For measuring cutting tools, e.g. screw taps, cutters, reamers.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Friction coupling for consistent, repeatable measuring force
- Prism angle 60°

Delivery:

Includes box, setting standard, adjustment wrench



Art. no.	32016 466
Brand	MITUTOYO
Manufacturer Part Number	114-165
Min./max. length measuring range	5-25 mm
Vernier scale	0.01 mm
Measuring surface diameter	6.3 mm
Measuring spindle increments	0.5 mm
Opening angle	60 Degree
Spindle clamping	Yes
Error limit	4 µm
Display	Nonius
Type	Five-flute V-anvil
Calibration Group	D, E
Gross Weight	0.360 kg
Product Group	3MA

EAN

4946368010366