

## Thread limit ring gauge

For Whitworth pipe threads DIN EN 10226/ISO 7-1 R

**ORION**<sup>®</sup>

### Application:

For testing the flank and core diameter of male threads.

### Execution:

- For threads that comply with the current standard DIN EN 102226

|                                 |   |
|---------------------------------|---|
| <b>Art. no.</b>                 | <b>32744 120</b>                        |
| <b>Brand</b>                    | ORION                                   |
| <b>Manufacturer Part Number</b> | 32744120                                |
| <b>Thread type</b>              | Tapered external pipe thread, Whitworth |
| <b>Pipe thread code</b>         | 4"-11                                   |
| <b>Material</b>                 | Gauge steel                             |
| <b>Calibration Group</b>        | AT                                      |
| <b>Gross Weight</b>             | 3.028 kg                                |
| <b>Product Group</b>            | 3DB                                     |



### EAN

4053625779116