

Wide-span rack

zinc-plated, with chipboard panels. Bolted or boltless



Application:

Wide-span racks offer large storage areas for bulky parts and particularly large and/or heavy items.

META wide-span racks - the boltless **META SPEED RACK** or the bolted **META MINI-RACK** - are ideal for storing bulky goods of light to medium weight in trade, industry and crafts. They can be used across different industries in a variety of ways. Both systems are available with either chipboard shelves or steel shelves.

Execution:

- Basic rack, can be expanded as required using an add-on rack
- Goods can be stored in a lying or standing position
- Shelves adjustable in increments of 50 mm
- Step struts with a 200 mm perforation grid to accommodate separator bars
- Insert shelf: Natural chipboard



Art. no.	50165 060
Brand	META
Manufacturer Part Number	20051243
Height	2200 mm
Length	1970 mm
Depth	1050 mm
Nominal length	1800 mm
Type of shelving	Shelving unit
Design	With particle board
Type of assembly	Screw mounting
Surface	Zinc plated
ESD-capable	No
Design of the frame	Disassembled
Grid dimension	50 mm
Number of shelves	3 PCS
Load-carrying capacity per shelf	600 kg
Load-carrying capacity per field	3200 kg
Number of frame	2 PCS
Made in	Germany
Gross Weight	119.000 kg
Product Group	508

EAN

4026212057775