

CAT 6, S/FTP Patchkabel
CAT 6, S/FTP Patch Cord

- Außenmantel: LSZH
- Aderquerschnitt: AWG 27/7
- Innenleiter: Kupfer (Cu)
- Schirmung: S/FTP (gesamt geflechtgeschirmt, paarweise foliengeschirmt)
- Transparent Rot gefärbter Stecker mit Metallschirmung
- Hauben mit Knickschutz, Zugentlastung und Rasthebelschutz
- Steckverbinder: FCC & IEC 60603-7-5
- Litzen-Innenleiter: 0,127 +/- 0,005 mm
- Außendurchmesser: 5,7 +/- 0,3 mm
- Isolierung Litzen-Innenleiter: FO-PE
- Betriebstemperaturbereich: -20 °C bis zu +60 °C
- Flammtest: IEC 60332-1, IEC 61034
- PoE+ kompatibel

- Sheath: LSZH
- Wire cross-section: AWG 27/7
- Conductor: Copper (Cu)
- Shielding: S/FTP (complete braid shielding, pairs foil shielded)
- Transparent red colored plug with metal shielding
- Boots with kink protection, strain relief and latch protection
- Connector: FCC & IEC 60603-7-5
- Stranded wire: 0.127 +/- 0.005 mm
- Diameter cable jacket: 5.7 +/- 0.3 mm
- Isolation stranded wire: FO-PE
- Operating temperature range: -20 °C up to +60 °C
- Flame retardancy: IEC 60332-1, IEC 61034
- PoE+ compatible



Farbe Color Länge Length	Grau Grey	Blau Blue	Schwarz Black	Grün Green	Rot Red	Weiß White	Gelb Yellow
0,25 m	DK-1644-0025 4016032321477	DK-1644-0025/B 4016032321484	DK-1644-0025/BL 4016032321491	DK-1644-0025/G 4016032321507	DK-1644-0025/R 4016032321514	DK-1644-0025/WH 4016032321521	DK-1644-0025/Y 4016032321538
0,50 m	DK-1644-005 4016032321545	DK-1644-005/B 4016032321569	DK-1644-005/BL 4016032321576	DK-1644-005/G 4016032321593	DK-1644-005/R 4016032321590	DK-1644-005/WH 4016032321606	DK-1644-005/Y 4016032321613
1,00 m	DK-1644-010 4016032321620	DK-1644-010/B 4016032321637	DK-1644-010/BL 4016032321644	DK-1644-010/G 4016032321651	DK-1644-010/R 4016032321668	DK-1644-010/WH 4016032321675	DK-1644-010/Y 4016032321699
2,00 m	DK-1644-020 4016032321712	DK-1644-020/B 4016032321729	DK-1644-020/BL 4016032321743	DK-1644-020/G 4016032321767	DK-1644-020/R 4016032321781	DK-1644-020/WH 4016032321804	DK-1644-020/Y 4016032321828
3,00 m	DK-1644-030 4016032321842	DK-1644-030/B 4016032321866	DK-1644-030/BL 4016032321880	DK-1644-030/G 4016032321897	DK-1644-030/R 4016032321910	DK-1644-030/WH 4016032321934	DK-1644-030/Y 4016032321941
5,00 m	DK-1644-050 4016032321956	DK-1644-050/B 4016032322016	DK-1644-050/BL 4016032322039	DK-1644-050/G 4016032322023	DK-1644-050/R 4016032322030	DK-1644-050/WH 4016032322047	DK-1644-050/Y 4016032322054
7,00 m	DK-1644-070 4016032322061	DK-1644-070/B 4016032322078	DK-1644-070/BL 4016032322085	DK-1644-070/G 4016032322108	DK-1644-070/R 4016032322115	DK-1644-070/WH 4016032322139	DK-1644-070/Y 4016032322146
10,00 m	DK-1644-100 4016032322160	DK-1644-100/B 4016032322191	DK-1644-100/BL 4016032322214	DK-1644-100/G 4016032322221	DK-1644-100/R 4016032322245	DK-1644-100/WH 4016032322252	DK-1644-100/Y 4016032322276
15,00 m	DK-1644-150 4016032322290	DK-1644-150/B	DK-1644-150/BL	DK-1644-150/G	DK-1644-150/R	DK-1644-150/WH	DK-1644-150/Y
20,00 m	DK-1644-200 4016032322943	DK-1644-200/B	DK-1644-200/BL	DK-1644-200/G	DK-1644-200/R	DK-1644-200/WH	DK-1644-200/Y
25,00 m	DK-1644-250 4016032328025	DK-1644-250/B	DK-1644-250/BL	DK-1644-250/G	DK-1644-250/R	DK-1644-250/WH	DK-1644-250/Y
30,00 m	DK-1644-300 4016032328067	DK-1644-300/B	DK-1644-300/BL	DK-1644-300/G	DK-1644-300/R	DK-1644-300/WH	DK-1644-300/Y

Gelb hinterlegt = Ware ab Lager verfügbar
Yellow highlighted = Available from stock

Neutral hinterlegt = Ware auf Anfrage erhältlich
not highlighted = Available on request

