


Jabra®

Jabra LINK™ 14201-32

ELECTRONIC HOOK SWITCH

SOLUTION FOR NORTEL/AVAYA PHONES

The Jabra LINK™ 14201-32 enables remote Electronic Hook Switch Control (EHS) with Jabra wireless headsets and the Nortel/Avaya 1100 Series IP Phones with USB headset port.

Jabra wireless headsets with EHS functionality boost productivity as they provide the user with the ability to answer and end a call, while away from their desk.

THE EHS ADAPTER ALLOWS THE USERS TO:

- Hear ring tones
 - Answer and end calls
 - Adjust the volume
 - Mute the microphone
- All from their headset

All quite convenient, when they are up to 450 ft. away from their desk! The integration of desk phone and headset allows users to benefit from enhanced mobility and the ability to multitask while on a call. The wireless freedom improves work efficiency and ergonomics throughout the day.

HOW IT WORKS

The Jabra LINK 14201-32 is a plug-and-play solution that converts from the EHS standard used in Nortel/Avaya phones to the DHSG standard used in Jabra headsets – and vice versa.

COMPATIBILITY

The Jabra LINK 14201-32 is compatible with the Nortel/Avaya 1100 Series IP Phones with USB headset port and most Jabra wireless headsets. For more details see the specifications on page 2.

EASY TO UPGRADE

The Jabra LINK 14201-32 is software upgradable. Simply connect the EHS cable to the computer via the USB port and download free software from www.jabra.com/pcsuite.



1. Connect to AUX port on headset base
2. Connect to Telephone port on headset base
3. Plug-and-play USB connectivity with Nortel/Avaya phones

GN Netcom is a world leader in innovative headset solutions. GN Netcom develops, manufactures and markets its products under the Jabra brand name.

A BRAND BY


GN Netcom

JABRA® IS A REGISTERED TRADEMARK OF GN NETCOM A/S

WWW.JABRA.COM






SPECIFICATIONS

SPECIFICATIONS	
THE JABRA LINK™ 14201-32	Enables Electronic Hook Switch Control with Nortel/Avaya phones and Jabra headsets
Item number	14201-32
Length of cables	900 mm (35.43 inches)
Certification	CE, FCC, C-Tick, UL
Warranty	North America /APAC: One-year limited warranty. Europe: Two-year limited warranty

COMPATIBILITY	
Nortel/Avaya Phones	Nortel/Avaya IP phone 1120E Nortel/Avaya IP phone 1140E Nortel/Avaya IP phone 1165E
Jabra Headsets	Jabra PRO 9400 Series, Jabra GO 6470, Jabra GN9350, Jabra GN9350e, Jabra GN9330e

EHS FEATURES	
Answer call	Yes
End call	Yes
Ring tone in headset	Yes
Volume control	Yes
Mute control	Yes

	JABRA PRO 9400 SERIES Stay in touch around the office	JABRA GO 6470 Stay in touch wherever you are	JABRA GN9350e/ JABRA GN9330e Superior sound and lightweight comfort
Connectivity	 (Mobile phone only for Jabra PRO 9470)		 (PC only for Jabra GN9350e)
Range	Up to 150 m/450 feet**	Soft + Deskphone: Up to 100 m/300 feet** Mobile Phone: Up to 25 m/80 feet ***	Up to 120 m / 350 feet**
Boom Style	Jabra PRO 9470 – Midi Jabra PRO 9460 – Flex	Short	Midi
Touch Screen	Yes	Yes	No
Auto Set-up	Yes	Yes	No
Wideband Sound	Yes	Yes	Yes (Jabra GN9350e with USB connection)
2-mic Noise Blackout™	Yes	Yes	No
Full Hearing Protection	Yes	Yes	Yes
Wearing Styles in Box	Headband + Earhook + Neckband (Neckband only for Jabra PRO 9470)	Headband + Earhook****	Headband + Earhook + Neckband (Neckband only for Jabra GN9350e)
Conferencing	No	No	Yes/ No
EHS Solution	Jabra LINK 14201-32	Jabra LINK 14201-32	Jabra LINK 14201-32

* Range varies according to the environment in which the headset is used

** Range depends on the device with which the headset is connected

*** Neckband available as accessory