



RMMDA 11/24 OUTPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 8A

1 relay; 1 NO contact
8 A
24 V DC
with minus plug link

Safe separation (IEC 61140/EN 61140)

[Link to Product](#)**Illustration**



Product may differ from Image

Utilization category

AC-1	8 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	2.5 A (24 V DC); 0.4 A (110 V DC); 0.3 A (230 V DC)

Input

Connection voltage - current	24 V DC (21.6...26.4 V DC) - 13.5 mA
Plug link (supplied)	Art.-Nr. 90960
LED display	LED (red)

General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	5 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+50 °C
Dimensions H × W × D	82×12×68 mm

Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 8 A
Min. load current	100 mA
Power rating (voltage dependent)	max. 2000 VA/240 W
Switching frequency	max. 10 Hz
Contact material	Ag Ni
Energize/release/contact bounce time	10/15/2 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1