

M12-M12 ADAPTOR,4 POLE U TO I CONVERTER

Adapter
M12 - M12
Male straight to female straight
4-pole, shielded
Voltage/current converter



[Link to Product](#)

Illustration



Male

Female



Product may differ from Image

Form

42252

Technical Data

| | |
|-------------------------------|-----------------|
| Operating voltage | max. 24 V AC/DC |
| Operating current per contact | max. 4 A |

| | |
|-------------------|---|
| Locking of ports | Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing |
| Compression gland | Zinc die casting, matte nickel plated |
| Protection | IP67 inserted and tightened (EN 60529) |
| Material | PUR |
| Application | Voltage/current converter |

General data

| | |
|------------------------|--------------|
| Temperature range | -25...+85 °C |
| Test isolation voltage | 0.8 kVrms |

Commercial data

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85369010 |
| minimum order quantity | 1 |