

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050050](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: LOVOLT® 400W 120V/12V Workstation with 4 Receptacles 15A Breaker, 16/3 SOOW Cord Type, 1.83m (6.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General

| | |
|-----------------------------|------------------------------------|
| Product Family | Portable Lighting |
| Series | 130105 |
| NEMA Configuration | NEMA 5-15 |
| NEMA Rating | NEMA 3R |
| Outlet | 2 - 60W07 Non-NEMA Crow Foot |
| Overview | Specialty Lighting |
| Product Literature Order No | 987650-8052 |
| Product Name | Woodhead® |
| Type | Hand Lamps, Specialty Light |
| UPC | 78678862520 |
| Woodhead | Yes |

Physical

| | |
|-------------------------|--------------------|
| Cord Length - Primary | 1.83m (6.0') |
| Cord Length - Secondary | N/A |
| Depth | 80.01mm (3.150") |
| Duty | Industrial |
| Guard Included | No |
| Guard Type | N/A |
| Height | 206.25mm (8.120") |
| Length | 285.75mm (11.250") |
| Material - Guard | N/A |
| Packaging Type | Carton |
| Socket Construction | N/A |

Electrical

| | |
|-------------------------------|--------------|
| Bulb Type | N/A |
| Cord Type - Primary | 16/3 SOOW |
| Lamp Type | N/A |
| Lamp Wattage - Maximum | 400W |
| Lumens | N/A |
| On/Off Switch | No |
| Voltage (Fixture) - Maximum | 120VAC 60 HZ |
| Voltage (Secondary) - Maximum | 12V AC |

Material Info

| | |
|--------------------|---------|
| Engineering Number | 1640-12 |
|--------------------|---------|



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

| | |
|-----------------|--------------|
| China ROHS | Not Reviewed |
| ELV | Not Relevant |
| RoHS Phthalates | Not Reviewed |

Search Parts in this Series

[130105 Series](#)