

## collet chuck DIN6343 185E, hexagonal

**FAHRION®**  
FAR BEYOND PRECISION

### Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- concentricity
- $\varnothing$  1-10 mm  $\leq$  20  $\mu$ m
- $\varnothing$  11-30 mm  $\leq$  30  $\mu$ m
- $\varnothing$  31-60 mm  $\leq$  40  $\mu$ m
- Other designs and complete sets can be supplied on request.



<b>Art. no.</b>	<b>23343 240</b>
<b>Brand</b>	FAHRION
<b>Manufacturer Part Number</b>	10130032400
<b>Outer diameter</b>	84 mm
<b>Diameter</b>	66 mm
<b>Length</b>	110 mm
<b>Width across flats</b>	24 mm
<b>Profile shape</b>	Hexagon with transverse grooves
<b>Diameter 2</b>	66 mm
<b>Gross Weight</b>	1.375 kg
<b>Product Group</b>	235

### EAN

4054631008450