

Drill vices

Mechanical clamping system

ORION[®]

Application:

For light machining work on drill presses and pillar drills.

Execution:

- Made from grey cast iron
- Precise clamping thanks to long flat rail guide
- Clamping jaws with steps and vee blocks
- Operate by hand or by toggle lever

Delivery:

1 pc. Drill vice



Art. no.	28665 100
Brand	ORION
Manufacturer Part Number	28665100
Jaws width	105 mm
Clamping width	110 mm
Jaws height	30 mm
Jaws thickness	12 mm
Body length	240 mm
Body height	65 mm
Body width	200 mm
Max. length	345 mm
Height	65 mm
Max. flute spacing	163 mm
Min. flute spacing	145 mm
Chip flute width	13 mm
Weight	9 kg
Gross Weight	8.442 kg
Product Group	282

EAN

4039247171200