

Ultrasonic wall thickness gauge MTG 6

For separate measuring heads

elcometer

Application:

For non-destructive recording of the material thickness of a wide range of acoustically conductive materials such as metals, NF metals, ceramic, plastics, glass, etc. Ideal for monitoring corrosion and erosion on closed components and structures or those accessible only from one side, e.g. pipes, tanks, large metal sheets etc.

Execution:

- Robust ABS plastic housing
- Large, easy-to-read 2.4" colour display
- IP 54 degree of protection, splash-proof
- Integral zero disc
- Red/green LEDs on the housing, for displaying the upper and lower limit value
- Scan mode for uniform inspections

| | |
|--|----------------------------|
| Art. no. | 46100 120 |
| Brand | ELCOMETER |
| Manufacturer Part Number | MTG6DL |
| Min./max. Pulsed-Echo (P-E) measuring range | 0.63-500 mm |
| Min./max. Echo-Echo ThruPaint (E-E) measuring range | 2.54-25.4 mm |
| Resolution of wall thickness | 0.1 mm, 0.01 mm switchable |
| Gross Weight | 2.040 kg |
| Product Group | 451 |

