

Heavy-duty workbench, series VS with 4.2 tonne load capacity

Solid beechwood 3000 mm, 6 drawers with full extension, 2 doors



Application:

For 2 workstations

Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 80 x 80 x 3 mm, with brackets for screwing to the floor
- 3 drawers with 100% full extension on the left, 3 x front height 180 mm, 1 door, height 540 mm on the right per workstation



Art. no.	50202 059
Number of drawers	6 PCS
Working height	900 mm
Number of doors	2 PCS
Worktop width	3000 mm
Pullout type	Full extension
Worktop height	100 mm
Colour of front	Anthracite grey RAL 7016
Worktop depth	800 mm
Cabinet colour	Light grey RAL 7035
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Levelling	No
Lock type	DOM® locking system
Drawer front height	6 x 180 mm
Drawer width (inner dimension)	500 mm
Surface	Powder-coated
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	4200 kg
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of worktop	Solid beech
Central locking	Yes
Product Group	Prod. Gr. 502

EAN

4014641164317