

Floor grating

High-pressure polyethylene


Application:

For machine and workbench workstations.

Execution:

- Anti-slip and non-skid, can support loads of up to 40000 kg/m²
- Highly resistant against oils, acids, solvents and alkalis
- Easy to move individually in a longitudinal or transverse direction thanks to hook connections

Art. no.	50225 102
Manufacturer Part Number	WD170001
Surface structure	Serrated
Material	PE - Polyethylene
Length	1200 mm
Width	600 mm
Height	25 mm
With levelling wedge	Optional
Resistance against	Oil, Acid, Fats, Petrol, Coolant
Min. temperature resistance	-10 °C
Max. temperature resistance	+80 °C
Suitable for wet areas	Yes
Anti-fatigue	Yes
Non-slip	Yes
Colour	Orange
Gross Weight	0.400 kg
Product Group	5AD



EAN

5060 103535552