

Han-Modular ECO coupler IP65, PE version



Part number	09 14 001 0721
Specification	Han-Modular ECO coupler IP65, PE version
HARTING eCatalogue	https://b2b.harting.com/09140010721

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® ECO
Type of hood/housing	Cable to cable housing
Description of hood/housing	With PE identification (pin 1 = PE) With integrated cable gland

Version

Locking type	Snap-in latches
Size	Modular ECO
Version	Top entry
Cable entry	1x Integrated

Technical characteristics

Limiting temperature	-40 ... +85 °C
Tightening torque	3 Nm Cable gland
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
Cable diameter	6 ... 13 mm

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	2
Net weight	37.36 g
Country of origin	Germany
Customs tariff number	85389099