

5-Pin Field Wireable Connectors, Reverse Key

- Male and Female Connectors
- IEC IP67 Protection



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p>BMWS 81..</p>	BMWS 8151-0/9	BMSWS 8151-0/9	Nickel Plated Brass, PG9 cable gland, accepts 6-8 mm cable diameter, screw terminal, accepts up to 18 AWG conductors, 85°C, 60 V, 4 A, Metal, fully shielded, mates with <u>reverse</u> key 5-pin cordsets and receptacles	<p>Female</p>
<p>BMSWS 81..</p>				
<p>BMWS 82..</p>	BMWS 8251-0/9	BMSWS 8251-0/9	Nickel Plated Brass, PG9 cable gland, accepts 6-8 mm cable diameter, screw terminal, accepts up to 18 AWG conductors, 85°C, 60 V, 4 A, metal, fully shielded, mates with <u>reverse</u> key 5-pin cordsets and receptacles	<p>Male</p>
<p>BMSWS 82..</p>				