

Product information

03 07 250

Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General	
Article No.	03 07 250
EAN	4003773015345
Pliers	chrome-plated
Head	chrome-plated
Handles	with dipped insulation, VDE-tested
Weight	597 g
Dimensions	250 x 73 x 36 mm
Standard	DIN ISO 5746 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 15.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm ²
VDE tested	yes

technical change and errors excepted