

## TDMX cutting body MS (M)



### Application:

First choice for stainless steel and heat-resistant alloy applications

### Execution:

- Precision-ground indexable insert, tip angle 140°

<b>Art. no.</b>	<b>11225 215</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	6568984
<b>Cutting edge diameter</b>	21.5 mm
<b>Indexable insert type</b>	F
<b>Carbide type</b>	WM15PD
<b>Surface</b>	TiAlN
<b>Cutting material</b>	SC
<b>Angle of the tip</b>	140 Degree
<b>Gross Weight</b>	0.026 kg
<b>Product Group</b>	1XA

