

## Haloflex 36° wide beam lamp

Work lamp

### Execution:

- Multi-purpose low voltage lamp with flexible lamp arm
- Powerful luminosity and glare-free light for precise work
- Safety transformer integrated in the base of the lamp
- Switch integrated in the lamp head
- Lamp head and housing made from impact-resistant, non-flammable plastic
- Connection line 1.6 m H03RN-F, 230 V
- Base height 88 mm, lamp-head length 83.5 mm
- Halogen lamp 12 V/20 Watt/G4 base
- Including safety glass cover and reinforced connecting cable

### Delivery:

With connection cable, magnet, screw clamps, screws

<b>Art. no.</b>	<b>56880 010</b>
<b>Power rating</b>	20 W
<b>Arm length</b>	420 mm
<b>IP protection class</b>	IP 20
<b>Gross Weight</b>	1.900 kg
<b>Product Group</b>	51D

