

PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PBT
 FLAMABILITY RATING: UL94-V0
 COLOR: WHITE
 CONTACT MATERIAL: COPPER ALLOYS
 CONTACT TYPE: STAMPED
 CONTACT PLATING: SELECTIVE GOLD
 SHIELDING: BRASS Ni PLATED
 QUALITY CLASS: 1500 MATING CYCLES

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 1A
 WORKING VOLTAGE: 30V
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 750V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX


SOLDERING
 WAVE PROCESS ONLY

PACKAGING
 TRAY

RoHS Compliant

G	23-MAR-09	NEW DRAW	JP
F	11-AUG-08	PINING	JP
E	07-APR-08	DRAWING	CH
D	05-DEC-07	MODIFICATIONS	EC
C	10-NOV-06	CT	JP
B	01-APR-04	ROHS	JP
A	19-JAN-99	PDF	JP
REV	DATE	FILE	BY

PROJECTION:



APPROVAL: RJ

GENERAL TOLERANCE

.X = +/- 0.2
 .XX = +/- 0.15



DESCRIPTION: DUAL USB TYPE A VERTICAL

WERI PART NO: 61400826021

SIZE

A4