

Coaxial Cable Connector 11_SMA-50-2-15/111_N

Description

Straight cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0022 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing	DOU-00006099
Assembly instruction	DOC-0000178687

Ordering Information

Single package	11_SMA-50-2-15/111_NE
Bulk 100 pcs package	11_SMA-50-2-15/111_NH
Single package	11_SMA-50-2-15/111_NE-1

Additional Information

Suitable cables	EZ_86_TP_M17, SUCOFORM_86, MULTIFLEX_86
-----------------	-----------------------------------------