



# 20850-144 PROPACPRO FRONT PANEL, FULL WIDTH, UNSHIELDED, 4 U, 84 HP, 2.5 MM, AL, ANODIZED, UNTREATED EDGES





# **KEY FEATURES**

Al panel, 2.0 mm (84 HP 2.5 mm)

## **PRODUCT ATTRIBUTES**

Accessory Type: Front panel
Material: Aluminum
Front Finish: Anodized
Rear Finish: Anodized
Treated Edges: No
Rack Height: 4 U
Rack Width: 84 HP
Height: 172.9 mm
Width: 452 mm
Depth: 2.5 mm
Package Quantity: 1

# ADDITIONAL PRODUCT DETAILS

The front panel, full width for PropacPRO Case mounts to the frame of the case.



#### **North America**

All locations +1.763.422.2661 Chat with us: schroff.nvent.com

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

nVent.com

### Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

#### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

Our powerful portfolio of brands:

nVent reserves the right to change specifications without notice.