




AMMDU OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 53 VDC / 1 A - 1 C/O contact

Transistor 1 A
24 V DC
with minus plug link

electr. NO/NC contact

[Link to Product](#)**Illustration**



Product may differ from Image

Input

Voltage range ON	10...53 V DC
Voltage range OFF	0...6 V DC
Input current	10 mA
LED display	LED (red)

General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	12×82×68 mm

Output

Switching voltage	4.5...53 V DC
Switching current per output	1 mA...1 A
Saturation voltage (across output)	max. 0.5 V DC
Leakage current (output is open)	max. 0.3 mA
Switching time ON/OFF	25/75 μs

Switching frequency	max. 1 kHz/10 Hz (resist./ind.)
---------------------	---------------------------------

Commercial data

country of origin	CZ
-------------------	----

customs tariff number	85414090
-----------------------	----------

minimum order quantity	1
------------------------	---