

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192030388**
Status: **Active**
Overview: High-Temperature Temp Terms Terminals and Splices
Description: Krimptite Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification 194130096-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series 19203
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview High-Temperature Temp Terms Terminals and Splices
Product Name Krimptite
Type Ring
UPC 822348424771

Physical

Barrel Type Closed
Insulation None
Material - Metal Steel
Material - Plating Mating Nickel
Net Weight 0.653/g
Packaging Type Carton
Stud Size 10 (M5)
Temperature Range - Operating 483°C
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 4.19mm max.
Wire Size AWG 14, 16
Wire Size mm² 1.50-2.50

Material Info

Reference - Drawing Numbers

Product Specification 194130096-000, PS-19902-011-001,
PS-19902-013-001
Sales Drawing SD-19203-017



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19203 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand	<u>640030100</u>
Crimp Tool	
Crimp Head for the	<u>640070100</u>
AT-200 Pneumatic	
Hand Tool	