

GROUNDING LUG

GL35 - Part No. 9819830



Wire Range

- #350kcmil - #6 AWG CU/AL Wire
- See tables below for Flexible stranded approvals

Electrical Ratings:

- 310A copper wire, 250A aluminum wire (Based on NEC code, 75°C wire)


Agency Compliance

- UL Recognized Wire Connector, UL File No. ZMNV2.E43665
- Supplemental UL Certification: Grounding and Bonding Equipment (KDER)
- Final acceptance of this component is dependent upon its installation and use in complete equipment submitted to UL
- CSA Certified, CSA File No. 63510-25 (Wire Classes B & C only)
- RoHS Compliant

Material Information

- Connector: Aluminum, tin plated
- Terminal screws: Steel, nickel plated - painted green

Termination Specifications

Wire Opening	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	350 kcmil - 6	375 lbf in	1	B, C, G, H, I

Drawing

