

## PCLN clamp holder, negative, left

For face and longitudinal turning with CN indexable insert

**ATORN**<sup>®</sup>

### Application


For longitudinal and face turning with CN indexable insert, 80°

### Version

- Precision-manufactured steel support, burnished, hardened, toggle-joint clamping system, type C, working angle 95°, tip angle 80°, clearance angle 0°

### Advantage

- Universal use for face and longitudinal turning with large feed depths and unfavourable conditions
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations



<b>Art. No.</b>	<b>17837 058</b>
<b>ISO name</b>	PCLN R/L 4040 S19
<b>Shaft height</b>	40 mm
<b>Shank width</b>	40 mm
<b>Length</b>	250 mm
<b>Length of head</b>	45 mm
<b>Programming size</b>	50 mm
<b>Suitable for indexable inserts</b>	CN.. 1906..
<b>Tool design</b>	Left
<b>DIN</b>	4983

### EAN-Code

4050293347906