



Solution Starters

P10 18-65W SIN 220-240V BL

Premium quality glow switch starter for igniting conventional electromagnetic fluorescent lamps in arctic conditions

Product data

• General Characteristics

System Description	Single
Cap-Base Information	2P
Color of the Housing	Blue

• Electrical Characteristics

Lamp Wattage	18-65 W
Voltage	220-240 V
Pulse Voltage	900 (min) V
Non Reclosure Voltage	140 (min) V
Capacitor	Yes

• Luminaire Design Requirements

Ambient Temperature	-40 (min), 75 (max) C
---------------------	-----------------------

• Product Dimensions

Overall Length C	40.3 (max) mm
------------------	---------------


Overall Width E	21.5 (max) mm
-----------------	---------------

• Product Data

Order code	928393700095
Full product code	928393700095
Full product name	P10 18-65W SIN 220-240V BL
Order product name	P10 18-65W SIN 220-240V BL/4X25CT
Pieces per pack	1
Packing configuration	4X25CT
Packs per outerbox	100
Bar code on pack - EAN1	8711500902344
Bar code on intermediate packing - EAN2	8711500902351
Bar code on outerbox - EAN3	8711500904010
Logistic code(s) - 12NC	928393700095
Net weight per piece	7.000 gr

PHILIPS

Dimensional drawing



P10 18-65W SIN 220-240V BL

Product	C (Max)	E (Max)
P10 18-65W SIN 220-240V BL	40.3	21.5



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, October 31
data subject to change