



# PrimaVision Mini for CDM

## HID-PV m 35/I CDM 220-240V 50/60Hz


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

### Product data

Operating and Electrical		Approval and Application	
Input Voltage	220 to 240 V	Approval Marks	F-Marking CE marking ENEC certificate CB Certificate
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	0.5 mA		
Inrush Current Width	0.25 ms		
Inrush Current Peak (Max)	15 A		
Number of Products on MCB (16A Type B) (Nom)	24		
Wiring		Product Data	
Cable Length From Device to Lamp	2 m	Order product name	HID-PV m 35/I CDM 220-240V 50/60Hz
Connector Type	Insert	Full product name	HID-PV m 35/I CDM 220-240V 50/60Hz
		Full product code	872790089164500
		Order code	913700653566
		Material Nr. (12NC)	913700653566
		Numerator - Quantity Per Pack	1
		Net Weight (Piece)	0.230 kg
		EAN/UPC - Product/Case	8711500881724
		Numerator - Packs per outer box	10
		EAN/UPC - Case	8727900891645
Temperature			
Ambient temperature range	-20 °C to 45 °C		
T-Case Lifetime (Nom)	85 °C		
T-Case Maximum (Max)	85 °C		
Mechanical and Housing			
Housing	Independent		

# PrimaVision Mini for CDM

## Dimensional drawing



Product	D1	C1	A1	A2	A3	B1
HID-PV m 35/I CDM 220-240V 50/60Hz	4.8 mm	34.0 mm	234.7 mm	225.1 mm	202.0 mm	49.4 mm

