

FEATURES

- Flexible - can be wrapped around pipes
- Various lengths available
- Cut to length

RS PRO 15W/m Trace Heating Cable Constant Wattage, Parallel Circuit, 240 V, 20m

RS Stock No.: 256-244



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO range of parallel circuit heating tape, with a constant wattage output for process temperature maintenance applications. This tape is flexible enough to allow it to be spiralled around a suitable pipe or vessel. The heating tape consists of several short heating zones each connected across a pair of continuous bus-wire conductors.

Trace heating options include:

- [703-3108](#) - 15W/m, 110 V, 20m cable
- [703-3101](#) - 15W/m, 110 V, 50m cable
- [703-3105](#) - 15W/m, 110 V, 100m cable
- [256-244](#) - 15W/m, 240 V, 20m cable
- [665-7419](#) - 15W/m, 240 V, 50m cable
- [665-7413](#) - 15W/m, 240 V, 100m cable
- [256-109](#) - Trace Heating Termination Kit

General Specifications

Cable Type	Constant Wattage; Parallel Circuit
Self-Regulating	No
Sheath Material	Silicone Rubber
Standard Met	BS EN 62395-1:2006, RoHS Compliant
Applications	Frost protection; Water, oil and chemical lines; Sprinkler system mains; Supply piping; Not for use in hazardous areas

Electrical Specifications

Output Per Metre	15W
Voltage Rating	240V

Mechanical Specifications

Length	20m
---------------	-----

Operation Environment Specifications

Operating Temperature Rating	-60 to 200°C
------------------------------	--------------



