


Diamant-Nassbohrkronen


Ø mm	Beschreibung	Geeignet für		A Werkzeug- aufnahme	B Arbeits- länge mm	C Gesamt- länge mm	Art.-Nr. 4932	EAN- Code 4002395
		DD 3-152	DCM2-250C DCM2-350C					
8	WCHP-SB 8	✓	◆	½" G	70	135	352072	367269
12	WCHP-SB 12	✓	◆	½" G	200	265	352074	367283
14	WCHP-SB 14	✓	◆	½" G	300	365	352075	367290
15	WCHP-SB 15	✓	◆	½" G	300	365	352076*	367306
16	WCHP-SB 16	✓	◆	½" G	300	365	352077	367313
18	WCHP-SB 18	✓	◆	½" G	300	365	352078	367320
20	WCHP-SB 20	✓	◆	½" G	300	365	352079	367337
22	WCHP-SB 22	✓	◆	½" G	300	365	352080	367344
24	WCHP-SB 24	✓	◆	½" G	300	365	352081	367351
25	WCHP-SB 25	✓	◆	½" G	300	365	352082	367368
28	WCHP-SB 28	✓	◆	½" G	300	365	352083	367375
30	WCHP-SB 30	✓	◆	½" G	300	365	352084	367382
32	WCHP-SB 32	✓	◆	½" G	300	365	352085	367399
35	WCHP-SB 35	✓	◆	½" G	300	365	352086	367405
37	WCHP-SB 37	✓	◆	½" G	300	365	352087	367412
40	WCHP-SB 40	✓	◆	½" G	300	365	352088	367429
42	WCHP-SB 42	✓	◆	½" G	300	365	352089	367436
45	WCHP-SB 45	✓	◆	½" G	300	365	352090	367443
50	WCHP-SB 50	✓	◆	½" G	300	365	352092	367467
52	WCHP 52		✓	1¼" UNC	420	500	399707	363582
	WCHP-SB 52	✓		1¼" UNC	420	500	352734	373925
62	WCHP 62		✓	1¼" UNC	420	500	399708	363599
	WCHP-SB 62	✓		1¼" UNC	420	500	352735	373932
72	WCHP 72		✓	1¼" UNC	420	500	399709	363605
82	WCHP 82		✓	1¼" UNC	420	500	399710	363612
	WCHP-SB 82	✓		1¼" UNC	420	500	352736	373949
92	WCHP 92		✓	1¼" UNC	420	500	399711	363629
	WCHP-SB 92	✓		1¼" UNC	420	500	352737	373956
102	WCHP 102		✓	1¼" UNC	420	500	399712	363636
	WCHP-SB 102	✓		1¼" UNC	420	500	352738	373963
112	WCHP 112		✓	1¼" UNC	420	500	399713	363643
	WCHP-SB 112	✓		1¼" UNC	420	500	352739	373970
122	WCHP 122		✓	1¼" UNC	420	500	399714	363650
	WCHP-SB 122	✓		1¼" UNC	420	500	352740	373987
132	WCHP 132		✓	1¼" UNC	420	500	399715	363667
	WCHP-SB 132	✓		1¼" UNC	420	500	352741	373994
152	WCHP 152		✓	1¼" UNC	420	500	399716	363674
	WCHP-SB 152	✓		1¼" UNC	420	500	352742	374007
162	WCHP 162		✓	1¼" UNC	420	500	399717	363681
172	WCHP 172		✓	1¼" UNC	420	500	352052	367092
182	WCHP 182		✓	1¼" UNC	420	500	399718	363698
202	WCHP 202		✓	1¼" UNC	420	500	399719	363704
225	WCHP 225		✓	1¼" UNC	420	500	399720	363711
250	WCHP 250		✓	1¼" UNC	420	500	399721	363728
300	WCHP 300		✓	1¼" UNC	420	500	399722	363735
350	WCHP 350		✓	1¼" UNC	420	500	399723	363742

✓ Sehr gute Arbeitsergebnisse. ◆ Geeignet.
* solange der Vorrat reicht

WCHP-SB
Ø 8–50 mm



WCHP-SB
Ø 52–152 mm



WCHP
Ø 52–350 mm

