




YVDAA042--S0001H03STGH050MSS

Connection technology



Product characteristics

Y connection cable

M12 plug / valve plug type A (according to DIN EN 175301-803)

Free from halogen

Electrical data

Electrical design

Operating voltage [V]

Oversvoltage protection VDR

Environment

Ambient temperature [°C]

Protection

Mechanical data

Design

Material body

Material nut

Weight [kg]

Displays / operating elements

Output status indication LED

Electrical connection

Connection

Sheath colour

DC

10...30 DC

•

-25...90

IP 65

straight / angled

TPU

Brass; nickel-plated

0.17




2 x yellow

PUR cable / 1 m;

3 x 0.5 mm² (16 x Ø 0.2 mm); Ø 4.8 mm; halogen-free

black

Wiring



Accessories

Accessories (included)

screw; tag for labelling

Remarks

Pack quantity [piece]

1