

## INTELLIGENT INTERFACE RELAY MODULE

RMI 11/24-230 VAC/DC, 1 C/O



Screw terminals

1 relay; 1 NO/NC contact

24...230 V AC/DC

[Link to Product](#)

### Illustration



Product may differ from Image

**Utilization category**

AC-1	8 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	1.1 A (24 V DC); 0.15 A (110 V DC)

**Input**

Connection voltage - current	24...230 V AC/DC (21.6...253 V AC/DC) - 7 mA; max. 30 mA
LED display	LED (red)

**General data**

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	6 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-25...+50 °C (storage temperature -40...+80 °C)

**Output**

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 8 A
Min. load current	100 mA
Power rating (voltage dependent)	max. 2000 VA/240 W
Switching frequency	max. 0.1 Hz (with load)
Contact material	Ag Ni
Energize/release/contact bounce time	8/20/2 ms

**Commercial data**

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1