




Datenblatt - Fiche technique - Data sheet


21.15.2761



ROLINE Patchkabel Kat.6A UTP, Component Level, LSOH, weiss, 1,0 m

Cordon ROLINE UTP Cat.6A / 10 Gigabit, Component Level, LSOH, blanc, 1,0 m

ROLINE UTP Patch Cord Cat.6A, Component Level, LSOH, white, 1.0 m



1. ELECTRICAL TEST:

- (1).100% OPEN SHORT & MISS WIRE TEST;
- (2).INSULATION RESISTANCE:DC 250V 20M OHM MIN;
- (3).CONTACTOR RESISTANCE:30 OHM MAX

2.PRINTING:GHMT® roline CAT.6A U/UTP COMPONENT PATCH CORD LSZH 500MHZ ISO/IEC

11801 & EN 50173-1 & ANSI/TIA-568-C.2

3.100% Component Patch cord Test PASS

4.Minimum bending radius:60mm

MATERIAL LIST

⑥	LABEL	NO DRY GLUE LABEL	1PCS	
⑤	MINI TIE	PE MINI TIE(POSSESS METAL)	2PCS	
④	POLYETHYLENE BAG	POLYETHYLENE BAG	1PCS	
③	OVER MOLD	88A PVC White	2PCS	
②	CONNECTOR	RJ45 8P8C'S UNSHIELDED PIN GOLD PLATED 3u", Transparent Blue	2PCS	
①	CABLE	S/FTP CAT.6A 26AWG (BC*1P+AL-FOIL)*4P+BRAID CABLE JACKET LSOH OD=6.2±0.2MM	1PCS	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

COLOUR:White		
ITEM NO.	LENGTH(L)	TOLERANCE(T)
21.15.2987	300mm	±10mm
21.15.2760	500mm	±15mm
21.15.2761	1000mm	±30mm
21.15.2764	1500mm	±45mm
21.15.2762	2000mm	±60mm
21.15.2763	3000mm	±90mm
21.15.2765	5000mm	±150mm
21.15.2766	7500mm	±210mm
21.15.2767	10000mm	±300mm
21.15.2768	15000mm	±450mm
21.15.2769	20000mm	±600mm

ITEM NO.	21.15.2987	21.15.2760	21.15.2761	21.15.2762	21.15.2763
21.15.2764	21.15.2765	21.15.2766	21.15.2767	21.15.2768	21.15.2769
DESC.	ROLINE U/UTP PatchCord CAT.6A, LSOH, Comp.Level,White				



		NEW		2016-09-13	A
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.