



Sample photo

Order symbol: ALN 121208
Product nbr: 7811210
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016102
EI. number:
 Finland: 3420048
 Electric No. 8212045680
 Denmark:
 Electric No. Sweden: 2536319

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	125	124	81	ARH 12	DIN-35 Mounting rail
inch:	4.9	4.9	3.2	MR 75005	Selftapping taptite screw M5
Materials:				MRS 28541	Wall fastening lug (2 pcs)
Material:	Aluminium			PH A & AH A/B	Hinge set
Base colour:	RAL 7001			Rating:	
Cover screws material:	Stainless steel			Ingress Protection (EN 60529): IP66/IP67/IP68	
Cover colour:	RAL 7001			Impact Resistance (EN 62262): IK08	
Gasket material:	Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperatures:				Certificates:	
Temperature °C (short term):	-50 ... 140 °C			SGS Fimko	
Temperature °C (continuous):	-50 ... 80 °C				
Temperature °F (short term):	-60 ... 285 °F				
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:					
AM 1212	Mounting plate				

