

T18L0M4



Article Number: 111-02015

Standard Cable Tie, 8" Long, 18lb Tensile Strength, PA66, Black, 1000/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T18L0M4

Type T18L

Color Black (BK)

- Features and Benefits**
- Inside serrations allow for strong hold on cables and wire bundles.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Standard Cable Tie, 8" Long, 18lb Tensile Strength, PA66, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 18.0 lbs

Minimum Tensile Strength (Metric) 80.0 N

Length L (Imperial) 8.0 "

Length L (Metric) 205.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.1 "

Width W (Metric) 2.5 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 2.17 "

Bundle Diameter Max. (Metric) 55.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 1000

Carton Quantity 10000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes