

Product information

78 03 125

Electronic Super Knips®

DIN ISO 9654



- Cutting edge hardness approx. 54 HRC
- INOX tool steel
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter




General

Article No.	78 03 125
EAN	4003773035381
Head	polished
Handles	with multi-component grips
Weight	56 g
Dimensions	125 x 65 x 13 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.6 mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm



technical change and errors excepted

