

LED PANEL MOUNT INDICATOR

RECESSED BEZEL, DC OPERATION

MOUNTING HOLE, Ø 8mm

PART NO.	COLOR	VOLTAGE V _{OP} [V] DC	CURRENT I _{OP typ.} [mA] DC	LUMI. INTENSITY LED I _{V typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
SATIN CHROME BEZEL					
WL-19050251	GREEN	12V	20	40	568
WL-19050252	YELLOW	12V	20	40	588
WL-19050253	RED	12V	20	80	625
WL-19050257	BLUE	12V	20	90	466
WL-1905025W	WHITE	12V	20	450	*
WL-19050351	GREEN	24V	20	40	568
WL-19050352	YELLOW	24V	20	40	588
WL-19050353	RED	24V	20	80	625
WL-19050357	BLUE	24V	20	90	466
WL-1905035W	WHITE	24V	20	450	*
WL-19050451	GREEN	28V	20	40	568
WL-19050452	YELLOW	28V	20	40	588
WL-19050453	RED	28V	20	80	625
WL-19050457	BLUE	28V	20	90	466
WL-1905045W	WHITE	28V	20	450	*
BLACK CHROME BEZEL					
WL-19051251	GREEN	12V	20	40	568
WL-19051252	YELLOW	12V	20	40	588
WL-19051253	RED	12V	20	80	625
WL-19051257	BLUE	12V	20	90	466
WL-1905125W	WHITE	12V	20	450	*
WL-19051351	GREEN	24V	20	40	568
WL-19051352	YELLOW	24V	20	40	588
WL-19051353	RED	24V	20	80	625
WL-19051357	BLUE	24V	20	90	466
WL-1905135W	WHITE	24V	20	450	*
WL-19051451	GREEN	28V	20	40	568
WL-19051452	YELLOW	28V	20	40	588
WL-19051453	RED	28V	20	80	625
WL-19051457	BLUE	28V	20	90	466
WL-1905145W	WHITE	28V	20	450	*

*Chromaticity coordinates X=0.31 Y=.032


NOTES

- Maximum panel thickness 6.5mm
- Storage temperature
T_{STG}: -25°C – +80°C
- Ambient temperature
T_A: -20°C – +60°C
- DC operation only
- Voltage tolerance
V_{OP}: ±10%
- Electro-optical ratings at
T_A=25°C
- Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
- Mounting hole
8 + 0.2mm
- 2.8 x 0.8mm terminals are standard
- Due to production tolerances, slight color variations may be detected within individual consignments
- Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M8 nut
- CAUTION: Do not solder directly to terminals

CERTIFICATIONS

RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

P: (714) 545-5560 F: (714) 545-6093

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM

WL-1905XX5X Series Rev 2