

PRODUCT-DETAILS

PSBF0430

LOW ACID PVC CVRD CONDUIT 20MM 30M



Product image
not available

General Information

Extended Product Type	PSBF0430
Product ID	7TCA297020R0312
EAN	5011949216693
Catalog Description	LOW ACID PVC CVRD CONDUIT 20MM 30M
Long Description	Liquid Tight, Pliable Conduit, Nominal Conduit Size 20mm, 1/2 Inch US Trade Size, Outside Diameter 21.0mm, Inside Diameter 14.6mm, Static Bend Radius 35mm, Reel Length 30 Meters, IP66, IP67 Rating, Galvanised Steel and Kraft Paper Core with PVC Covering, Black

Ordering

EAN	5011949216693
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	20.48 lb 9.288 kg
--------------------	----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Indoors / Outdoors, Marine, Buildings, Infrastructure
Brand / Label	Kopex
Color	Black
Inside Diameter	14.6 mm
Material	Galvanized Steel and Kraft Paper Core with PVC Covering
Nominal Size	1/2 in NC20
Number of Batteries	0
Outside Diameter	21.0 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Liquid Tight Pliable Conduit
Radius	35 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210243887

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	PSBF0430
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	PSBF0430

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available