

Die, HSS MF right, pre-slotted and 1.75 thread chamfer

for universal use up to 700 N/mm²

ORION[®]

Application:

For cutting fine metric threads externally in the material groups of steel and non-ferrous metals up to a strength of 700 N/mm².

Execution:

- right die, tol. 6 g with spiral point, pre-slotted and 1.75 pitch

Advantage:

- standard geometry with excellent price/performance ratio

Art. no.	13445 060
Brand	ORION
Manufacturer Part Number	13445060
Thread type	Metric fine thread
Cutting material	HSS
Tolerance of dies	6 g
Thread type x nominal diameter	MF6
Pitch	0.5 mm
Outer diameter	20 mm
Height	5 mm
Cutting direction	Right-hand cutting
Gross Weight	0.007 kg
Product Group	1DC



EAN

4039247073535