

Electronic 3-point quick internal micrometer set

IP67



Application:

For measuring through-bores and blind bores (from Ø 12.5 mm) and short centring shoulders in series production.

Execution:

- Self-centring and self-aligning
- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Max./min. value memory
- HOLD function
- Preset function
- Tolerance function

Advantage:

- Pistol grip for quick measurements using retractable lever

Delivery:

1 measuring element, measuring heads with setting rings, battery (1 x 3 V lithium type CR 2032)



Art. no.	31919 520
Brand	SYLVAC
Manufacturer Part Number	955.6105
Min./max. length measuring range	20-50 mm
Measuring depth	55/80 mm
Error limit	3 µm
Data transmission type	Bluetooth/Proximity
Digit increment	0.001 mm
IP protection class	IP 67
Adjusting ring diameter	35 mm, 20 mm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Gross Weight	3.400 kg
Product Group	317

EAN

7640125028744