

T1 individual test pin

Diameter 7.00-7.99 mm / graduation 0.01 mm

ORION[®]

Application:

For measuring bore hole clearances, bore diameters, angularity of bores etc.



Execution:

- Ground and lapped
- Hardened 60-64 HRC
- Diameter of 0.300 to 0.999 mm with a length of 40 mm; from diameter 1.000 mm with a length of 70 mm
- from diameter 3.00 mm: One end with 30-45° chamfer; other end deburred with diameter marking on end face
- diameter from 1.5 to 2.999 mm: One end with 30-45° chamfer; other end deburred with diameter marking on outer surface
- diameter from 1.00 to 1.499 mm: One end with 30-45° chamfer; other end deburred without diameter marking
- up to 0.999 mm: both ends deburred, without diameter marking

Art. no.	32481 753
Brand	ORION
Manufacturer Part Number	32481753
Diameter	7.53 mm
Tolerance class	1
Material	Gauge steel
Length	70 mm
DIN	2269
Calibration Group	AE
Gross Weight	0.020 kg
Product Group	3DA

EAN

4039247193608