

META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, zinc plated



Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



| | |
|---|------------------|
| Art. no. | 50167 753 |
| Brand | META |
| Manufacturer Part Number | 20070739 |
| Height | 3000 mm |
| Length | 1306 mm |
| Depth | 436 mm |
| Nominal length | 1300 mm |
| Nominal depth | 400 mm |
| Design | Double-sided |
| Type of assembly | To insert |
| Surface | Zinc plated |
| ESD-capable | No |
| Design of the frame | Pre-assembled |
| Grid dimension | 25 mm |
| Number of shelves | 6 PCS |
| Load-carrying capacity per shelf | 230 kg |
| Load-carrying capacity per field | 1900 kg |
| Number of frame | 1 PCS |
| Number of lines | 2 |
| Quality label | RAL-RG 614/1 |
| Made in | Germany |
| Material | Steel |
| Gross Weight | 80.881 kg |
| Product Group | 508 |

EAN

4026212102239