

Accessories

LED spacer \varnothing 3mm / \varnothing 5mm



- temperature resistance of approx. 140°C
- material: PC-GV (polycarbonate) grey
- tolerance for length ± 0.1 mm
- RoHS compliant





for 3mm LED`s

Length (mm)	Part No.
3.0mm	546.71.03
4.0mm	546.71.04
5.0mm	546.71.05
6.0mm	546.71.06
7.0mm	546.71.07
8.0mm	546.71.08
9.0mm	546.71.09
10.0mm	546.71.10
11.0mm	546.71.11
12.0mm	546.71.12
13.0mm	546.71.13
14.0mm	546.71.14
15.0mm	546.71.15
16.0mm	546.71.16
17.0mm	546.71.17
18.0mm	546.71.18
19.0mm	546.71.19
20.0mm	546.71.20
21.0mm	546.71.21
22.0mm	546.71.22
23.0mm	546.71.23
24.0mm	546.71.24
25.0mm	546.71.25

for 5mm LED`s

Length (mm)	Part No.
3.0mm	325.71.03
4.0mm	325.71.04
5.0mm	325.71.05
6.0mm	325.71.06
7.0mm	325.71.07
8.0mm	325.71.08
9.0mm	325.71.09
10.0mm	325.71.10
11.0mm	325.71.11
12.0mm	325.71.12
13.0mm	325.71.13
14.0mm	325.71.14
15.0mm	325.71.15
16.0mm	325.71.16
17.0mm	325.71.17
18.0mm	325.71.18
19.0mm	325.71.19
20.0mm	325.71.20
21.0mm	325.71.21
22.0mm	325.71.22
23.0mm	325.71.23
24.0mm	325.71.24
25.0mm	325.71.25



1. All specifications according to information from our manufacturers, without additional guarantee on our part
2. All dimensions are in millimetres
3. Specifications are subject to change without notice