


**DESIGN**  
Hot tin-plated steel enclosures for High/Frequency electronic components assembly. Volume of casing is suitable for easy assembly of professional and High-Technology circuits.


**TRIPLATE**



**DESIGN**  
An electrolytic tin-plated steel enclosures for High/Frequency electronic components assembly with two slide-on covers. It has one removable horizontal divider that separates the enclosure into two sections. It also has vertical dividers with holes for wiring. Volume of casing is suitable for easy assembly of professional and High-Technology circuits.



**MICRO**



**DESIGN**  
Electrolytic tin-plated steel enclosures for High/Frequency electronic components assembly with a cover that can be soldered on for hermetic sealing. Volume of casing is suitable for easy assembly of professional and High-Technology circuits.

	Part-No	Ext. Dimensions			Material
		L	W	H	
	Hot tin plated				
	-				
37	371.16 *	54	50	26	STEEL
	372.16 *	83	50	26	STEEL
	373.16 *	106	50	26	STEEL
	374.16 *	161	50	26	STEEL
39	392.16 *	83	68	28	STEEL
	393.16 *	122	68	28	STEEL
	394.16 *	161	68	28	STEEL
27	271.16 *	54	50	26	STEEL
	272.16 *	83	50	26	STEEL
	273.16 *	106	50	26	STEEL
	274.16 *	161	50	26	STEEL
	292.16 *	83	68	27	STEEL
29	293.16 *	122	68	27	STEEL
	294.16 *	161	68	27	STEEL
	1661.16 *	67,5	68	17	STEEL
16	1680.16 *	82,5	68	17	STEEL
	16120.16 *	122	68	17	STEEL
	16160.16 *	161	68	17	STEEL

	Part-No	Ext. Dimensions			Material
		L	W	H	
	Hot tin plated				
	-				
Pcb	3710.16 *	54	50	19	STEEL
	4020.16 *	54	29	16	STEEL
	402.16 *	54	29	21	STEEL
Mini	403.16 *	80	29	21	STEEL
	404.16 *	105	29	21	STEEL
	405.16 *	130	29	21	STEEL
	406.16 *	155	29	21	STEEL

	Part-No	Ext. Dimensions			Material
		L	W	H	
	Electrolytic tin plated				
	-				
Triplate	395.15 *	61,5	76	36	STEEL
	396.15 *	101	76	36	STEEL
	397.15 *	161	76	36	STEEL
	398.15 *	221	76	36	STEEL
	399.15 *	281	76	36	STEEL
	433.15 *	50,5	31,5	9,5	STEEL
Micro	434.15 *	63,5	31,5	9,5	STEEL
	435.15 *	50,5	44	9,5	STEEL
	436.15 *	63,5	44	9,5	STEEL
	443.15 *	50,5	31,5	13	STEEL
	444.15 *	63,5	31,5	13	STEEL
	445.15 *	50,5	44	13	STEEL
	446.15 *	63,5	44	13	STEEL
	453.15 *	50,5	31,5	17,5	STEEL
	454.15 *	63,5	31,5	17,5	STEEL
	455.15 *	50,5	44	17,5	STEEL
456.15 *	63,5	44	17,5	STEEL	