

## Han-Modular ECO hood IP65 (without PE)



Part number	09 14 001 0420
Specification	Han-Modular ECO hood IP65 (without PE)
HARTING eCatalogue	<a href="https://b2b.harting.com/09140010420">https://b2b.harting.com/09140010420</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® ECO
Type of hood/housing	Hoods
Description of hood/housing	With integrated cable gland

### Version

Locking type	Snap-in latches
Size	Modular ECO
Version	Top entry
Cable entry	1x Integrated

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Tightening torque	3 Nm Cable gland
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
Cable diameter	6 ... 13 mm

### Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances No

---

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

---

## Commercial data

Packaging size	2
Net weight	42.83 g
Country of origin	Germany
Customs tariff number	85389099

---