


PRODUCT SPECIFICATION

Brand	KASP
Product Range	High Security Combination Padlocks
Catalogue number	119
Date	22/06/2012

Range Description High security re-settable combination padlocks	
Features <ul style="list-style-type: none">• Supertough Molybdenum Steel Shackle - Extra protection against hacksaw & cropping attacks• Hardened Steel Electro-plated Lock Body - Extra strength & resistance against corrosion• Double Bolted Locking Mechanism - Extra strength to resist torsion & pull attacks• Anti Manipulation Locking System - Protects against manipulation attack• 4 Dial Re-settable Combination – Re-settable combination for added convenience & security• Rust Free Internal Components & Dual Drainage System - Extra resistance against corrosion Closed Shackle <ul style="list-style-type: none">• Closed Shackle - Additional shackle protection to resist shackle attack <p>Available in open and close shackle options.</p> <p>These padlocks are supplied display packed, in sealed blister packs.</p>	

Technical product information

Body – Hardened steel body, black electro-plated

Shackle – Hardened molybdenum steel, chrome plated

Locking mechanism - Double bolted, 4 dial combination locking mechanism featuring an anti-manipulation locking system to prevent intelligent manipulation attack. All internal components are rust free.

To open the padlock:

1) Using the correct combination code, open the padlock by aligning the dial wheels with the indicators on the lock body (pre-set factory combination code 0-0-0-0) and depress the shackle

To lock the padlock:

1) Whilst in the open position, scramble the dial wheels and depress the shackle into the body of the padlock until it locks

To reset the lock to a combination of your choice:

1) Open the padlock using the preset combination code

2) Insert the change key into the keyhole on the side of the padlock

3) Firmly press the key into the keyhole and turn 90 degrees clockwise or anti-clockwise. *[IMPORTANT: Ensure the change key is fully depressed to avoid losing the combination]*

4) With the change key held at 90 degrees, reset the dials wheels to a combination of your choice (we recommend that you record your new combination code and store it in a safe place)

5) With your new combination code set, turn the change key through 90 degrees back to its original position and withdraw it from the key hole

6) Lock the padlock by scrambling the dial wheels and depressing the shackle into the body of the padlock until it locks

Security rating:

Type	Security rating
K11960D	10
K11960XD	11

Shackle Dimensions:

Dimensions mm	Shackle			Body
	Dia	Internal width	Internal height	Width
K11960D	11	21	28	62
K11960XD	11	21	30	62

Use environment - Normal outdoor use √√

Recommended applications- Gates, garages, shutters, vehicles, site gates

Standards compliance

None applicable

User health and safety

None applicable

information	
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K11960D	62	35	90	640	117	38	186	728
K11960XD	62	35	90	663	117	38	186	751