


# Crimp Fittings

# Press-armaturen

# Embouts sertis

# Raccordi a graffare

# Racores para presión



**FJA**  
 J.I.C Female Swivel, 45° Elbow  
 JIC-Dichtkopf, 45° Krümmer  
 Femelle JIC coudé 45°  
 Femmina girevole JIC a 45°  
 Hembra loca JIC acodado a 45°

Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G3FJA3	1S3FJA3	1A3FJA3	3/8-24				-3	48,7	31,2	13,9	2,5	14		
1G4FJA3	1S4FJA3	1A4FJA3	7/16-20				-3	43,7	26,2	8,4	2,5	14		
1G4FJA4	1S4FJA4	1A4FJA4	7/16-20				-4	45,1	21,7	8,4	3,9	14		
1G5FJA4	1S5FJA4	1A5FJA4	1/2-20				-4	51,9	28,5	9,3	4,2	17		
1G5FJA5	1S5FJA5	1A5FJA5	1/2-20				-5	52,7	28,8	9,3	4,6	17		
1G6FJA5	1S6FJA5	1A6FJA5	9/16-18				-5	53,9	30,0	9,9	5,3	19		
1G6FJA6	1S6FJA6	1A6FJA6	9/16-18				-6	58,6	33,3	9,9	6,2	19		
1G8FJA6	1S8FJA6	1A8FJA6	3/4-16				-6	67,4	42,1	13,9	6,7	22		
1G8FJA8	1S8FJA8	1A8FJA8	3/4-16				-8	71,7	42,0	14,0	9,4	22		
1G10FJA8	1S10FJA8	1A10FJA8	7/8-14				-8	76,9	47,2	15,1	9,6	27		
1G10FJA10	1S10FJA10	1A10FJA10	7/8-14				-10	74,8	45,4	15,1	11,7	27		
1G12FJA10	1S12FJA10	1A12FJA10	1 1/16-12				-10	85,9	56,5	19,8	12,8	32		
1G12FJA12	1S12FJA12	1A12FJA12	1 1/16-12				-12	87,1	56,9	19,8	14,8	32		
1G16FJA12	1S16FJA12	1A16FJA12	1 5/16-12				-12	90,3	60,3	27,1	15,5	41		
1G16FJA16	1S16FJA16	1A16FJA16	1 5/16-12				-16	95,1	60,7	27,9	19,3	41		
1G20FJA20	1S20FJA20	1AP20FJA20*	1 5/8-12				-20	112,9	68,9	31,0	25,7	50		
		1AT20FJA20**	1 5/8-12				-20	112,8	68,8	31,0	26,6	50		
	1S24FJA24		1 7/8-12				-24	124,2	77,9	36,2	32,0	60		

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

Specification subject to change without notice