



**SVS ECO LED VALVE PLUG FORM B 10 MM LED VDR 110V**

2+PE field-wireable M16x1.5

Form B (10 mm)  
110 V AC/DC with LED and VDR  
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Height: 31 mm

Product may differ from Image

### Approvals



### Form

29645

### Technical Data

Operating voltage	110 V AC/DC (95...121 V AC/DC)
Operating current per contact	max. 1.5 A
Connection cross section	0.5...1.5 mm <sup>2</sup>
Sealing range (cable diameter)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16 × 1.5 mm
Contact figure	Cable outlet can be turned in 180° steps
Protection	IP65 inserted and tightened

### General data

Temperature range	-40...+60 °C
-------------------	--------------

### Commercial data

country of origin	HU
customs tariff number	85366990
minimum order quantity	1