

SIVACON, base, EMC, IP40, D: 500 mm, W: 800 mm, galvanized



Figure similar

Model	
Product brand name	SIVACON
Design of the product	EMC
Design of the surface	galvanized
Design of the product / EMC version	Yes
Protection class IP	IP40
Product component	No
<ul style="list-style-type: none"> • ventilation 	
Mechanical Design	
Width	800 mm
Depth	500 mm
Net weight	4 600 g
Equipment marking	
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 	U
<ul style="list-style-type: none"> • acc. to DIN EN 81346-2 	UC

EMC	Declaration of Conformity	Test Certificates	other
Miscellaneous	 EG-Konf.	Special Test Certificate	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1085-2UB32-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1085-2UB32-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1085-2UB32-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



