

UT131A

Compacte Multimeter

| Specificaties | | |
|--------------------------------------|--|----------------------|
| Basisfuncties | Bereik | Beste nauwkeurigheid |
| DC spanning | 200mV/2V/20V/200V/250V | $\pm(0.8\%+1)$ |
| AC spanning | 200mV/2V/20V/200V/250V | $\pm(1.0\%+2)$ |
| AC stroom | 200 μ A/2000 μ A/20mA/ 200mA/2A/10A | $\pm(1.2\%+3)$ |
| DC stroom | 200 μ A/2000 μ A/20mA/ 200mA/2A/10A | $\pm(1.0\%+3)$ |
| Weerstand | 200 Ω /2k Ω /20k Ω /200k Ω /2M Ω /20M Ω /200M Ω | $\pm(0.8\%+2)$ |
| Capaciteit | 2nF/20nF/200nF/2 μ F/ 20 μ F/200 μ F | $\pm(3\%+5)$ |
| Speciale functies | | |
| Maximale display uitlezing | 1999 | |
| Bereik keuze | Automatisch | |
| Valtest | 2m | |
| Diodetest | ✓ | |
| Doorbelttest | ✓ | |
| Overbelasting alarm | ✓ | |
| Data hold | ✓ | |
| Relatieve meting | ✓ | |
| Lage batterijspanning indicatie | ✓ | |
| Automatische achtergrond verlichting | ✓ | |
| Automatische uitschakeling | ✓ | |
| Veiligheidsklasse | CAT II 250V | |
| Algemene eigenschappen | | |
| Voeding | 2 x AAA Batterijen 1.5V | |
| Standaard accessoires | Handleiding, meetsnoeren, holster | |
| Gewicht | 206g (inclusief batterijen) | |
| Afmetingen | 134×77×47mm | |

