

Stepladders

Single-sided access



Version:

- Patented step design: robust, stable, durable, flanged step-rail connection
- High-strength Perlon straps with sewn-in fixing clip to prevent splay (7 or more steps)
- Closed step profile and integrated guide tube
- Optimum platform stability thanks to extruded aluminium profile
- Two bridge lifts made of extruded sections
- Practical storage tray with lots of space for tools and small parts

Advantage:

- Stable footing thanks to non-slip plastic shoes
- Large-surface standing platform with anti-slip grooves

Art. no.	50260 544
Number of steps (including platform)	1 x 7
Working height	3.5 m
Length	2.26
Platform height	1.48 m
Pedestal width	0.51 m
Weight	9.1 kg
Accessibility	One-sided
Material	Aluminium
With storage tray	Yes
Folding	Yes
EN standard	131



EAN-Code

4003866424573